

Designed by Komplot Design

PRODUCT



Item no.: 21001-1A-XX
+ style code



DESCRIPTION

The GUBI Chair Collection is a chair series in laminated moulded 3-D veneer or in the injection moulded HiRek material. The shell is 5 mm thick. Both types of the shells can be delivered upholstered, with front upholstered or fully upholstered in fabric or leather. The base is available in steel, in different finishes as specified below and moulded wood in various finishes. Several of the chair versions are stackable. The GUBI Chair series includes a side chair with and without arms, a bar stool, a lounge chair and a table series in 3 different heights.

VERSION - HIREK

RAL codes are indicative.

- Black / Chrome base // RAL 9004, silkmatt / -
- White / Chrome base // RAL 9003, silkmatt / -
- Misty Grey / Chrome base // RAL 140 70 05, silkmatt / -
- Midnight Grey / Chrome base // RAL 7012, silkmatt / -
- Blue Morning / Chrome base // RAL 210 80 10, silkmatt / -
- Orange Sweet / Chrome base // RAL 040 60 60, silkmatt / -

- Black / Satin chrome base // RAL 9004, silkmatt / -
- White / Satin chrome base // RAL 9003, silkmatt / -
- Misty Grey / Satin chrome base // RAL 140 70 05, silkmatt / -
- Midnight Grey / Satin chrome base // RAL 7012, silkmatt / -
- Blue Morning / Satin chrome base // RAL 210 80 10, silkmatt / -
- Orange Sweet / Satin chrome base // RAL 040 60 60, silkmatt / -


- Black / Black painted base // RAL 9004, silkmatt / RAL 9005, gloss level 30
- White / Black painted base // RAL 9003, silkmatt / RAL 9005, gloss level 30
- Misty Grey / Black painted base // RAL 140 70 05, silkmatt / RAL 9005, gloss level 30
- Midnight Grey / Black painted base // RAL 7012, silkmatt / RAL 9005, gloss level 30
- Blue Morning / Black painted base // RAL 210 80 10, silkmatt / RAL 9005, gloss level 30
- Orange Sweet / Black painted base // RAL 040 60 60, silkmatt / RAL 9005, gloss level 30

CHAIR VERSION

Order item - look for part number in the pricelist.

The series consists of the following:

GUBI 1A, GUBI 12A, GUBI 13A



COLOURS



// Black



// White



// Misty Grey



// Midnight Grey



// Blue Morning



// Orange Sweet

FACTS

MEASUREMENT - L X W X H MM

Sitting height: 458 mm
Seat width: 493 mm
Seat depth: 544 mm
Seat height: 483 mm
Back height: 373 mm
Frame width: 576 mm
Frame depth: 499 mm
Chair height: 807 mm
Shell thickness: 5 mm
Frame thickness: Ø11 mm

WEIGHT ITEM

5,400 kg

PACKAGING TYPE

Cardboard box

PACKAGING MEASUREMENT - L X W X H CM

L:59 X W:55 X H:84 CM

WEIGHT PACKAGING - MATERIAL TYPE

- Delivery note: 5 g
- Cardboard box, FEFCO quality EB85BB: 2192 g
- Cardboard extra bottom: 408 g
- Polybag PE: 200 g
- LD-EPE foam protector: 100 g
- Strapping: 10 g

WEIGHT PACKAGING - TOTAL

8,315 kg

NUMBER OF PARCELS

1 pcs.


- Defective frame and shells can be replaced.

Designed by Komplot Design

ACCESSORIES

FELT GLIDERS FOR HARD FLOOR AVAILABLE ON REQUEST.

TROLLEY, LINKING DEVICE, CHAIR SUSPENSION FOR TABLES.



CLEANING AND MAINTENANCE

For dusting and light cleaning of the plastic surface and frame use a soft, dry cloth.

For further cleaning, use a soft cloth that is firmly wrung in clean water for gently wiping the surface, and then immediately use a dry cloth to wipe the surface again.

If more thorough cleaning is necessary, use a mild detergent or washing-up liquid dissolved in water on a firmly wrung cloth. Afterwards, repeat the process with clean water as described above.

Polish with a soft cloth after wiping.

Do not use materials for maintenance that:

- Contain abrasive agents.
- Are basic, acidiferous or organic.

For the best maintenance of the product, protect it against sunlight and heat, and try to keep it away from moisture, grease and other dirt.

Furthermore, protect the surfaces against sharp objects and other that might scratch.

ENVIRONMENT

Parts can be separated and sorted for recycling.

Disposal of plastic type PP may be done with incineration of waste.

TESTS

EN 15373:2007 Furniture - Strength, durability and safety - Requirements for non-domestic Seat. Loading according to Test severity 2. General use.

CERTIFICATION AND LABELS

-